

**FAG****X-life****23218-E1-XL-K-TVPB-C3** [🔗](#)**Spherical Roller Bearing**

Spherical roller bearings 232...-E1-K, main dimensions to DIN 635-2, with tapered bore, taper 1:12

Technical information**Your current product variant**

Design	E1	Without central rip
Bore type	K	Tapered, taper 1:12
Cage	TVPB	Plastic cage
Radial internal clearance	C3 (Group 3)	Internal clearance larger than CN
Relubrication	Standard	

Main Dimensions & Performance Data

d	90 mm	Bore diameter
D	160 mm	Outside diameter
B	52,4 mm	Width
C _r	445.000 N	Basic dynamic load rating, radial
C _{0r}	520.000 N	Basic static load rating, radial
C _{ur}	50.000 N	Fatigue load limit, radial
n _G	4.250 1/min	Limiting speed
n _{gr}	2.650 1/min	Reference speed
≈m	4,106 kg	Weight



Mounting dimensions

$d_{a \min}$	101 mm	Minimum diameter shaft shoulder
$D_{a \max}$	149 mm	Maximum diameter of housing shoulder
$r_{a \max}$	2 mm	Maximum recess radius
$B_{a \min}$	18 mm	Minimum cavity width of the sleeve
$d_{a \max}$	104 mm	Maximum diameter of shaft shoulder
$d_{b \min}$	100 mm	Minimum cavity diameter of the sleeve

Dimensions

$r_{\min}$	2 mm	Minimum chamfer dimension
D_1	140 mm	Bore diameter outer ring
d_2	104,1 mm	Raceway diameter of the inner ring
d_s	3,2 mm	Diameter lubrication hole
n_s	6,5 mm	Width of lubricating groove

Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	120 °C	Operating temperature max.

Calculation factors

e	0,31	Limiting value of F_a/F_r for the applicability of diff. Values of factors X and Y
Y_1	2,2	Dynamic axial load factor
Y_2	3,27	Dynamic axial load factor
Y_0	2,15	Static axial load factor

Additional information

H2318	Adapter sleeve
AHX3218	Withdrawal sleeve



Characteristics



Radial load



Axial load in one direction



Axial load in two directions



Grease Lubrication



Oil Lubrication



Not sealed



Static angular error and misalignment



Dynamic angular error and misalignment