



**FAG****22205-E1-XL**

Spherical Roller Bearing

Spherical roller bearings 222...-E1, main dimensions to DIN 635-2

X-life

Technical information



Your current product variant

Design	E1	Without central rip
Bore type	Z	Cylindrical
Cage	JPA	Sheet metal cage
Radial internal clearance	CN (Group N)	Normal internal clearance
Relubrication facility	Standard	

Main Dimensions & Performance Data

d	25 mm	Bore diameter
D	52 mm	Outside diameter
B	18 mm	Width
C_r	48.500 N	Basic dynamic load rating, radial
C_{0r}	42.500 N	Basic static load rating, radial
C_{ur}	4.900 N	Fatigue load limit, radial
n_G	14.400 1/min	Limiting speed
n_{gr}	9.200 1/min	Reference speed
$\approx m$	0,171 kg	Weight

Mounting dimensions

$d_{a \min}$	30,6 mm	Minimum diameter shaft shoulder
$D_{a \max}$	46,4 mm	Maximum diameter of housing shoulder
$r_{a \max}$	1 mm	Maximum recess radius



Dimensions

r _{min}	1 mm	Minimum chamfer dimension
D ₁	44,4 mm	Bore diameter outer ring
d ₂	31,5 mm	Raceway diameter of the inner ring
d _s	3,2 mm	Diameter lubrication hole
n _s	4,8 mm	Width of lubricating groove

Temperature range

T _{min}	-30 °C	Operating temperature min.
T _{max}	200 °C	Operating temperature max.

Calculation factors

e	0,33	Limiting value of Fa/Fr for the applicability of diff. Values of factors X and Y
Y ₁	2,07	Dynamic axial load factor
Y ₂	3,09	Dynamic axial load factor
Y ₀	2,03	Static axial load factor

Characteristics

-  Radial load
-  Axial load in one direction
-  Axial load in two directions
-  Grease Lubrication
-  Oil Lubrication
-  Not sealed
-  Static angular error and misalignment
-  Dynamic angular error and misalignment