



FAG



X-life

23218-E1-XL-TVPB

Spherical Roller Bearing

Spherical roller bearings 232...-E1, main dimensions to DIN 635-2

Technical information



Your current product variant

Design	E1	Without central rip
Bore type	Z	Cylindrical
Cage	TVPB	Plastic cage
Radial internal clearance	CN (Group N)	Normal internal clearance
Relubrication	Standard	

Main Dimensions & Performance Data

d	90 mm	Bore diameter
D	160 mm	Outside diameter
B	52,4 mm	Width
C _r	445.000 N	Basic dynamic load rating, radial
C _{0r}	520.000 N	Basic static load rating, radial
C _{ur}	50.000 N	Fatigue load limit, radial
n _G	4.250 1/min	Limiting speed
n _{gr}	2.650 1/min	Reference speed
≈m	4,228 kg	Weight



Mounting dimensions

d _{a min}	101 mm	Minimum diameter shaft shoulder
D _{a max}	149 mm	Maximum diameter of housing shoulder
r _{a max}	2 mm	Maximum recess radius

Dimensions

r _{min}	2 mm	Minimum chamfer dimension
D ₁	140 mm	Bore diameter outer ring
d ₂	104,1 mm	Raceway diameter of the inner ring
d _s	3,2 mm	Diameter lubrication hole
n _s	6,5 mm	Width of lubricating groove

Temperature range

T _{min}	-30 °C	Operating temperature min.
T _{max}	120 °C	Operating temperature max.

Calculation factors

e	0,31	Limiting value of Fa/Fr for the applicability of diff. Values of factors X and Y
Y ₁	2,2	Dynamic axial load factor
Y ₂	3,27	Dynamic axial load factor
Y ₀	2,15	Static axial load factor



Characteristics

-  Radial load
-  Axial load in one direction
-  Axial load in two directions
-  Grease Lubrication
-  Oil Lubrication
-  Not sealed
-  Static angular error and misalignment
-  Dynamic angular error and misalignment