



**FAG****22336-BE-XL-K**

Spherical Roller Bearing

Spherical roller bearings 223...-E1-K, main dimensions to DIN 635-2, with tapered bore, taper 1:12

X-life

Technical information



Your current product variant

Design	BE	With lose center lip ring
Bore type	K	Tapered, taper 1:12
Cage	JPB	Sheet metal cage
Radial internal clearance	CN (Group N)	Normal internal clearance
Relubrication	Standard	

Main Dimensions & Performance Data

d	180 mm	Bore diameter
D	380 mm	Outside diameter
B	126 mm	Width
C _r	2.060.000 N	Basic dynamic load rating, radial
C _{0r}	2.460.000 N	Basic static load rating, radial
C _{ur}	195.000 N	Fatigue load limit, radial
n _G	2.030 1/min	Limiting speed
n _{gr}	1.230 1/min	Reference speed
≈m	64,905 kg	Weight



Mounting dimensions

$d_{a \min}$	197 mm	Minimum diameter shaft shoulder
$d_{a \max}$	217 mm	Maximum diameter of shaft shoulder
$D_{a \max}$	363 mm	Maximum diameter of housing shoulder
$r_{a \max}$	3 mm	Maximum recess radius
$d_{b \min}$	195 mm	Minimum cavity diameter of the sleeve
$B_{a \min}$	8 mm	Minimum cavity width of the sleeve

Dimensions

$r_{\min}$	4 mm	Minimum chamfer dimension
D_1	320,8 mm	Bore diameter outer ring
d_2	224,9 mm	Raceway diameter of the inner ring
d_s	12,5 mm	Diameter lubrication hole
n_s	23,5 mm	Width of lubricating groove

Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	200 °C	Operating temperature max.

Calculation factors

e	0,34	Limiting value of F_a/F_r for the applicability of diff. Values of factors X and Y
Y_1	1,96	Dynamic axial load factor
Y_2	2,92	Dynamic axial load factor
Y_0	1,92	Static axial load factor

Additional information

H2336	Adapter sleeve
AH2336G	Withdrawal sleeve



Characteristics

-  Radial load
-  Axial load in one direction
-  Axial load in two directions
-  Grease Lubrication
-  Oil Lubrication
-  Not sealed
-  Large bearing
-  Static angular error and misalignment
-  Dynamic angular error and misalignment