


**FAG****24122-BE-XL**

Spherical Roller Bearing

Spherical roller bearing 241...-BE-XL,
symmetric with rib washer

X-life

Technical information



Your current product variant

Design	BE	With lose center lip ring
Bore type	Z	Cylindrical
Cage	JPB	Sheet metal cage
Radial internal clearance	CN (Group N)	Normal internal clearance
Relubrication	Standard	

Main Dimensions & Performance Data

d	110 mm	Bore diameter
D	180 mm	Outside diameter
B	69 mm	Width
C_r	530.000 N	Basic dynamic load rating, radial
C_{0r}	750.000 N	Basic static load rating, radial
C_{ur}	86.000 N	Fatigue load limit, radial
n_G	3.350 1/min	Limiting speed
n_{gr}	1.960 1/min	Reference speed
$\approx m$	6,709 kg	Weight

Mounting dimensions

$d_{a \min}$	121 mm	Minimum diameter shaft shoulder
$D_{a \max}$	169 mm	Maximum diameter of housing shoulder
$r_{a \max}$	2 mm	Maximum recess radius



Dimensions

r_{min}	2 mm	Minimum chamfer dimension
D_1	154,9 mm	Bore diameter outer ring
d_2	125,6 mm	Raceway diameter of the inner ring
d_s	3,2 mm	Diameter lubrication hole
n_s	6,5 mm	Width of lubricating groove

Temperature range

T_{min}	-30 °C	Operating temperature min.
T_{max}	200 °C	Operating temperature max.

Calculation factors

e	0,34	Limiting value of F_a/F_r for the applicability of diff. Values of factors X and Y
Y_1	1,96	Dynamic axial load factor
Y_2	2,92	Dynamic axial load factor
Y_0	1,92	Static axial load factor

Characteristics

	Radial load
	Axial load in one direction
	Axial load in two directions
	Grease Lubrication
	Oil Lubrication
	Not sealed
	Static angular error and misalignment
	Dynamic angular error and misalignment