



**FAG****24160-BE-XL-K30-C3**

Spherical Roller Bearing

Spherical roller bearings 241...-BE-K30, main dimensions to DIN 635-2, with tapered bore, taper 1:30

X-life

Technical information



Your current product variant

Design	BE	With lose center lip ring
Bore type	K30	Tapered, taper 1:30
Cage	JPB	Sheet metal cage
Radial internal clearance	C3 (Group 3)	Internal clearance larger than CN
Relubrication	Standard	

Main Dimensions & Performance Data

d	300 mm	Bore diameter
D	500 mm	Outside diameter
B	200 mm	Width
C _r	3.950.000 N	Basic dynamic load rating, radial
C _{0r}	6.400.000 N	Basic static load rating, radial
C _{ur}	500.000 N	Fatigue load limit, radial
n _G	1.100 1/min	Limiting speed
n _{gr}	450 1/min	Reference speed
≈m	153,2 kg	Weight

Mounting dimensions

d _{a min}	320 mm	Minimum diameter shaft shoulder
D _{a max}	480 mm	Maximum diameter of housing shoulder
r _{a max}	4 mm	Maximum recess radius



Dimensions

r _{min}	5 mm	Minimum chamfer dimension
D ₁	422,8 mm	Bore diameter outer ring
d ₂	338,2 mm	Raceway diameter of the inner ring
d _s	8 mm	Diameter lubrication hole
n _s	15 mm	Width of lubricating groove

Temperature range

T _{min}	-30 °C	Operating temperature min.
T _{max}	200 °C	Operating temperature max.

Calculation factors

e	0,39	Limiting value of Fa/Fr for the applicability of diff. Values of factors X and Y
Y ₁	1,72	Dynamic axial load factor
Y ₂	2,56	Dynamic axial load factor
Y ₀	1,68	Static axial load factor

Additional information

AH24160	Withdrawal sleeve
---------	-------------------



Characteristics

-  Radial load
-  Axial load in one direction
-  Axial load in two directions
-  Grease Lubrication
-  Oil Lubrication
-  Not sealed
-  Large bearing
-  Static angular error and misalignment
-  Dynamic angular error and misalignment