

**FAG****X-life****22217-E1-XL-K** **Spherical Roller Bearing**

Spherical roller bearings 222...-E1-K, main dimensions to DIN 635-2, with tapered bore, taper 1:12

Technical information**Your current product variant**

Design	E1	Without central rip
Bore type	K	Tapered, taper 1:12
Cage	JPA	Sheet metal cage
Radial internal clearance	CN (Group N)	Normal internal clearance
Relubrication facility	Standard	

Main Dimensions & Performance Data

d	85 mm	Bore diameter
D	150 mm	Outside diameter
B	36 mm	Width
C _r	305.000 N	Basic dynamic load rating, radial
C _{0r}	325.000 N	Basic static load rating, radial
C _{ur}	39.000 N	Fatigue load limit, radial
n _G	5.700 1/min	Limiting speed
n _{gr}	3.450 1/min	Reference speed
≈m	2,56 kg	Weight



Mounting dimensions

d _{a min}	96 mm	Minimum diameter shaft shoulder
d _{a max}	99 mm	Maximum diameter of shaft shoulder
D _{a max}	139 mm	Maximum diameter of housing shoulder
r _{a max}	2 mm	Maximum recess radius
d _{b min}	91 mm	Minimum cavity diameter of the sleeve
B _{a min}	12 mm	Minimum cavity width of the sleeve

Dimensions

r _{min}	2 mm	Minimum chamfer dimension
D ₁	135,4 mm	Bore diameter outer ring
d ₂	99,7 mm	Raceway diameter of the inner ring
d _s	3,2 mm	Diameter lubrication hole
n _s	6,5 mm	Width of lubricating groove

Temperature range

T _{min}	-30 °C	Operating temperature min.
T _{max}	200 °C	Operating temperature max.

Calculation factors

e	0,22	Limiting value of Fa/Fr for the applicability of diff. Values of factors X and Y
Y ₁	3,04	Dynamic axial load factor
Y ₂	4,53	Dynamic axial load factor
Y ₀	2,97	Static axial load factor

Additional information

H317	Adapter sleeve
AHX317	Withdrawal sleeve



Characteristics



Radial load



Axial load in one direction



Axial load in two directions



Grease Lubrication



Oil Lubrication



Not sealed



Static angular error and misalignment



Dynamic angular error and misalignment