



**FAG****21314-E1-XL-C3**

Spherical Roller Bearing

Spherical roller bearings 213...-E1, main dimensions to DIN 635-2

X-life

Technical information



Your current product variant

Design	E1	Without central rip
Bore type	Z	Cylindrical
Cage	JPA	Sheet metal cage
Radial internal clearance	C3 (Group 3)	Internal clearance larger than CN
Relubrication	Standard	

Main Dimensions & Performance Data

d	70 mm	Bore diameter
D	150 mm	Outside diameter
B	35 mm	Width
C _r	250.000 N	Basic dynamic load rating, radial
C _{0r}	270.000 N	Basic static load rating, radial
C _{ur}	34.500 N	Fatigue load limit, radial
n _G	6.200 1/min	Limiting speed
n _{gr}	3.950 1/min	Reference speed
≈m	3,06 kg	Weight

Mounting dimensions

d _{a min}	82 mm	Minimum diameter shaft shoulder
D _{a max}	138 mm	Maximum diameter of housing shoulder
r _{a max}	2,1 mm	Maximum recess radius



Dimensions

r_{min}	2,1 mm	Minimum chamfer dimension
D_1	126,2 mm	Bore diameter outer ring
d_2	94,9 mm	Raceway diameter of the inner ring
d_s	3,2 mm	Diameter lubrication hole
n_s	6,5 mm	Width of lubricating groove

Temperature range

T_{min}	-30 °C	Operating temperature min.
T_{max}	200 °C	Operating temperature max.

Calculation factors

e	0,22	Limiting value of F_a/F_r for the applicability of diff. Values of factors X and Y
Y_1	3,14	Dynamic axial load factor
Y_2	4,67	Dynamic axial load factor
Y_0	3,07	Static axial load factor

Characteristics

-  Radial load
-  Axial load in one direction
-  Axial load in two directions
-  Grease Lubrication
-  Oil Lubrication
-  Not sealed
-  Static angular error and misalignment
-  Dynamic angular error and misalignment