



**FAG****22315-E1-XL**

Spherical Roller Bearing

Spherical roller bearings 223...-E1, main dimensions to DIN 635-2

X-life

Technical information



Your current product variant

Design	E1	Without central rip
Bore type	Z	Cylindrical
Cage	JPA	Sheet metal cage
Radial internal clearance	CN (Group N)	Normal internal clearance
Relubrication	Standard	

Main Dimensions & Performance Data

d	75 mm	Bore diameter
D	160 mm	Outside diameter
B	55 mm	Width
C_r	445.000 N	Basic dynamic load rating, radial
C_{0r}	450.000 N	Basic static load rating, radial
C_{ur}	41.500 N	Fatigue load limit, radial
n_G	4.500 1/min	Limiting speed
n_{gr}	3.550 1/min	Reference speed
$\approx m$	5,286 kg	Weight

Mounting dimensions

$d_{a \min}$	87 mm	Minimum diameter shaft shoulder
$D_{a \max}$	148 mm	Maximum diameter of housing shoulder
$r_{a \max}$	2,1 mm	Maximum recess radius



Dimensions

r_{min}	2,1 mm	Minimum chamfer dimension
D_1	136,3 mm	Bore diameter outer ring
d_2	92,4 mm	Raceway diameter of the inner ring
d_s	4,8 mm	Diameter lubrication hole
n_s	9,5 mm	Width of lubricating groove

Temperature range

T_{min}	-30 °C	Operating temperature min.
T_{max}	200 °C	Operating temperature max.

Calculation factors

e	0,34	Limiting value of F_a/F_r for the applicability of diff. Values of factors X and Y
Y_1	1,99	Dynamic axial load factor
Y_2	2,96	Dynamic axial load factor
Y_0	1,94	Static axial load factor

Characteristics

-  Radial load
-  Axial load in one direction
-  Axial load in two directions
-  Grease Lubrication
-  Oil Lubrication
-  Not sealed
-  Static angular error and misalignment
-  Dynamic angular error and misalignment