



**FAG****22217-E1-XL-C4**

Spherical Roller Bearing

Spherical roller bearings 222...-E1, main dimensions to DIN 635-2

X-life

Technical information



Your current product variant

Design	E1	Without central rip
Bore type	Z	Cylindrical
Cage	JPA	Sheet metal cage
Radial internal clearance	C4 (Group 4)	Internal clearance larger than C3
Relubrication facility	Standard	

Main Dimensions & Performance Data

d	85 mm	Bore diameter
D	150 mm	Outside diameter
B	36 mm	Width
C _r	305.000 N	Basic dynamic load rating, radial
C _{0r}	325.000 N	Basic static load rating, radial
C _{ur}	39.000 N	Fatigue load limit, radial
n _G	5.700 1/min	Limiting speed
n _{gr}	3.450 1/min	Reference speed
≈m	2,601 kg	Weight

Mounting dimensions

d _{a min}	96 mm	Minimum diameter shaft shoulder
D _{a max}	139 mm	Maximum diameter of housing shoulder
r _{a max}	2 mm	Maximum recess radius



Dimensions

r _{min}	2 mm	Minimum chamfer dimension
D ₁	135,4 mm	Bore diameter outer ring
d ₂	99,7 mm	Raceway diameter of the inner ring
d _s	3,2 mm	Diameter lubrication hole
n _s	6,5 mm	Width of lubricating groove

Temperature range

T _{min}	-30 °C	Operating temperature min.
T _{max}	200 °C	Operating temperature max.

Calculation factors

e	0,22	Limiting value of Fa/Fr for the applicability of diff. Values of factors X and Y
Y ₁	3,04	Dynamic axial load factor
Y ₂	4,53	Dynamic axial load factor
Y ₀	2,97	Static axial load factor

Characteristics

-  Radial load
-  Axial load in one direction
-  Axial load in two directions
-  Grease Lubrication
-  Oil Lubrication
-  Not sealed
-  Static angular error and misalignment
-  Dynamic angular error and misalignment