

**FAG****X-life****22208-E1-XL-K** **Spherical Roller Bearing**

Spherical roller bearings 222...-E1-K, main dimensions to DIN 635-2, with tapered bore, taper 1:12

Technical information**Your current product variant**

Design	E1	Without central rip
Bore type	K	Tapered, taper 1:12
Cage	JPA	Sheet metal cage
Radial internal clearance	CN (Group N)	Normal internal clearance
Relubrication facility	Standard	

Main Dimensions & Performance Data

d	40 mm	Bore diameter
D	80 mm	Outside diameter
B	23 mm	Width
C _r	101.000 N	Basic dynamic load rating, radial
C _{0r}	91.000 N	Basic static load rating, radial
C _{ur}	12.100 N	Fatigue load limit, radial
n _G	10.500 1/min	Limiting speed
n _{gr}	6.200 1/min	Reference speed
≈m	0,505 kg	Weight



Mounting dimensions

$d_{a \min}$	47 mm	Minimum diameter shaft shoulder
$d_{a \max}$	48 mm	Maximum diameter of shaft shoulder
$D_{a \max}$	73 mm	Maximum diameter of housing shoulder
$r_{a \max}$	1 mm	Maximum recess radius
$d_{b \min}$	44 mm	Minimum cavity diameter of the sleeve
$B_{a \min}$	5 mm	Minimum cavity width of the sleeve

Dimensions

$r_{\min}$	1,1 mm	Minimum chamfer dimension
D_1	70,4 mm	Bore diameter outer ring
d_2	48,8 mm	Raceway diameter of the inner ring
d_s	3,2 mm	Diameter lubrication hole
n_s	4,8 mm	Width of lubricating groove

Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	200 °C	Operating temperature max.

Calculation factors

e	0,27	Limiting value of F_a/F_r for the applicability of diff. Values of factors X and Y
Y_1	2,49	Dynamic axial load factor
Y_2	3,71	Dynamic axial load factor
Y_0	2,43	Static axial load factor

Additional information

H308	Adapter sleeve
AH308	Withdrawal sleeve



Characteristics

-  Radial load
-  Axial load in one direction
-  Axial load in two directions
-  Grease Lubrication
-  Oil Lubrication
-  Not sealed
-  Static angular error and misalignment
-  Dynamic angular error and misalignment