

FAG



X-life

22326-E1-XL-K

Spherical Roller Bearing

Spherical roller bearings 223...-E1-K, main dimensions to DIN 635-2, with tapered bore, taper 1:12

Technical information



Your current product variant

Design	E1	Without central rip
Bore type	K	Tapered, taper 1:12
Cage	JPA	Sheet metal cage
Radial internal clearance	CN (Group N)	Normal internal clearance
Relubrication facility	Standard	

Main Dimensions & Performance Data

d	130 mm	Bore diameter
D	280 mm	Outside diameter
B	93 mm	Width
C _r	1.250.000 N	Basic dynamic load rating, radial
C _{0r}	1.370.000 N	Basic static load rating, radial
C _{ur}	120.000 N	Fatigue load limit, radial
n _G	2.650 1/min	Limiting speed
n _{gr}	1.820 1/min	Reference speed
≈m	26,709 kg	Weight



Mounting dimensions

$d_{a \min}$	147 mm	Minimum diameter shaft shoulder
$d_{a \max}$	162 mm	Maximum diameter of shaft shoulder
$D_{a \max}$	263 mm	Maximum diameter of housing shoulder
$r_{a \max}$	3 mm	Maximum recess radius
$d_{b \min}$	142 mm	Minimum cavity diameter of the sleeve
$B_{a \min}$	8 mm	Minimum cavity width of the sleeve

Dimensions

$r_{\min}$	4 mm	Minimum chamfer dimension
D_1	239,5 mm	Bore diameter outer ring
d_2	162,2 mm	Raceway diameter of the inner ring
d_s	9,5 mm	Diameter lubrication hole
n_s	17,7 mm	Width of lubricating groove

Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	200 °C	Operating temperature max.

Calculation factors

e	0,33	Limiting value of F_a/F_r for the applicability of diff. Values of factors X and Y
Y_1	2,06	Dynamic axial load factor
Y_2	3,06	Dynamic axial load factor
Y_0	2,01	Static axial load factor

Additional information

H2326	Adapter sleeve
AHX2326G	Withdrawal sleeve



Characteristics



Radial load



Axial load in one direction



Axial load in two directions



Grease Lubrication



Oil Lubrication



Not sealed



Static angular error and misalignment



Dynamic angular error and misalignment