



FAG



22328-E1-XL-K

Spherical Roller Bearing

Spherical roller bearings 223...-E1-K, main dimensions to DIN 635-2, with tapered bore, taper 1:12

X-life

Technical information



Your current product variant

Design	E1	Without central rip
Bore type	K	Tapered, taper 1:12
Cage	JPA	Sheet metal cage
Radial internal clearance	CN (Group N)	Normal internal clearance
Relubrication	Standard	

Main Dimensions & Performance Data

d	140 mm	Bore diameter
D	300 mm	Outside diameter
B	102 mm	Width
C _r	1.460.000 N	Basic dynamic load rating, radial
C _{0r}	1.630.000 N	Basic static load rating, radial
C _{ur}	135.000 N	Fatigue load limit, radial
n _G	2.420 1/min	Limiting speed
n _{gr}	1.660 1/min	Reference speed
m	33,629 kg	Weight



Mounting dimensions

$d_{a \min}$	157 mm	Minimum diameter shaft shoulder
$d_{a \max}$	169 mm	Maximum diameter of shaft shoulder
$D_{a \max}$	283 mm	Maximum diameter of housing shoulder
$r_{a \max}$	3 mm	Maximum recess radius
$d_{b \min}$	152 mm	Minimum cavity diameter of the sleeve
$B_{a \min}$	8 mm	Minimum cavity width of the sleeve

Dimensions

$r_{\min}$	4 mm	Minimum chamfer dimension
D_1	255,7 mm	Bore diameter outer ring
d_2	173,5 mm	Raceway diameter of the inner ring
d_s	9,5 mm	Diameter lubrication hole
n_s	17,7 mm	Width of lubricating groove

Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	200 °C	Operating temperature max.

Calculation factors

e	0,34	Limiting value of F_a/F_r for the applicability of diff. Values of factors X and Y
Y_1	2	Dynamic axial load factor
Y_2	2,98	Dynamic axial load factor
Y_0	1,96	Static axial load factor

Additional information

H2328	Adapter sleeve
AHX2328G	Withdrawal sleeve



Characteristics

-  Radial load
-  Axial load in one direction
-  Axial load in two directions
-  Grease Lubrication
-  Oil Lubrication
-  Not sealed
-  Static angular error and misalignment
-  Dynamic angular error and misalignment