



FAG



X-life

22315-E1-XL-T41A

Spherical Roller Bearing

Spherical roller bearing 223...-E1-XL-T41A,
symmetric with cage guidance ring

Technical information



Your current product variant

Design	E1	Without central rip
Bore type	Z	Cylindrical
Cage	JPA	Sheet metal cage
Radial internal clearance	C4 (Group 4)	Internal clearance larger than C3
Relubrication	Standard	
Spherical roller bearing for vibrating screens	T41A	For vibrating screens

Main Dimensions & Performance Data

d	75 mm	Bore diameter
D	160 mm	Outside diameter
B	55 mm	Width
C_r	445.000 N	Basic dynamic load rating, radial
C_{0r}	450.000 N	Basic static load rating, radial
C_{ur}	41.500 N	Fatigue load limit, radial
n_G	4.500 1/min	Limiting speed
n_{gr}	3.550 1/min	Reference speed
$\approx m$	5,255 kg	Weight



Mounting dimensions

$d_{a \min}$	87 mm	Minimum diameter shaft shoulder
$D_{a \max}$	148 mm	Maximum diameter of housing shoulder
$r_{a \max}$	2,1 mm	Maximum recess radius

Dimensions

$r_{\min}$	2,1 mm	Minimum chamfer dimension
D_1	136,3 mm	Bore diameter outer ring
d_2	92,4 mm	Raceway diameter of the inner ring
d_s	4,8 mm	Diameter lubrication hole
n_s	9,5 mm	Width of lubricating groove

Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	200 °C	Operating temperature max.

Calculation factors

e	0,34	Limiting value of F_a/F_r for the applicability of diff. Values of factors X and Y
Y_1	1,99	Dynamic axial load factor
Y_2	2,96	Dynamic axial load factor
Y_0	1,94	Static axial load factor



Characteristics



Radial load



Axial load in one direction



Axial load in two directions



Grease Lubrication



Oil Lubrication



Not sealed



Static angular error and misalignment



Dynamic angular error and misalignment