



FAG



X-life

22322-E1-XL-T41D

Spherical Roller Bearing

Spherical roller bearings 223...-E1-T41A,
For oscillating load with restricted diameter
tolerances

Technical information



Your current product variant

Design	E1	Without central rip
Bore type	Z	Cylindrical
Cage	JPA	Sheet metal cage
Radial internal clearance	C4 (Group 4)	Internal clearance larger than C3
Relubrication	Standard	
Spherical roller bearing for vibrating screens	T41D	For vibrating screens, bore thin layer chromium coated

Main Dimensions & Performance Data

d	110 mm	Bore diameter
D	240 mm	Outside diameter
B	80 mm	Width
C _r	950.000 N	Basic dynamic load rating, radial
C _{0r}	1.070.000 N	Basic static load rating, radial
C _{ur}	93.000 N	Fatigue load limit, radial
n _G	3.000 1/min	Limiting speed
n _{gr}	2.130 1/min	Reference speed
≈m	17,702 kg	Weight



Mounting dimensions

$d_{a \min}$	124 mm	Minimum diameter shaft shoulder
$D_{a \max}$	226 mm	Maximum diameter of housing shoulder
$r_{a \max}$	2,5 mm	Maximum recess radius

Dimensions

$r_{\min}$	3 mm	Minimum chamfer dimension
D_1	204,9 mm	Bore diameter outer ring
d_2	143,1 mm	Raceway diameter of the inner ring
d_s	8 mm	Diameter lubrication hole
n_s	15 mm	Width of lubricating groove

Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	200 °C	Operating temperature max.

Calculation factors

e	0,33	Limiting value of F_a/F_r for the applicability of diff. Values of factors X and Y
Y_1	2,07	Dynamic axial load factor
Y_2	3,09	Dynamic axial load factor
Y_0	2,03	Static axial load factor