



**FAG****22312-E1A-XL-M**

Spherical Roller Bearing

Spherical roller bearing 223...-E1A-XL-M,
symmetric 2 outer ribs

X-life

Technical information



Your current product variant

Design	E1A	Without central rip
Bore type	Z	Cylindrical
Cage	M	Brass Cage
Radial internal clearance	CN (Group N)	Normal internal clearance
Relubrication	Standard	

Main Dimensions & Performance Data

d	60 mm	Bore diameter
D	130 mm	Outside diameter
B	46 mm	Width
C _r	310.000 N	Basic dynamic load rating, radial
C _{0r}	310.000 N	Basic static load rating, radial
C _{ur}	29.000 N	Fatigue load limit, radial
n _G	5.400 1/min	Limiting speed
n _{gr}	4.200 1/min	Reference speed
≈m	2,875 kg	Weight

Mounting dimensions

d _{a min}	72 mm	Minimum diameter shaft shoulder
D _{a max}	118 mm	Maximum diameter of housing shoulder
r _{a max}	2,1 mm	Maximum recess radius



Dimensions

r _{min}	2,1 mm	Minimum chamfer dimension
D ₁	110,1 mm	Bore diameter outer ring
d ₂	74,8 mm	Raceway diameter of the inner ring
d _s	3,2 mm	Diameter lubrication hole
n _s	6,5 mm	Width of lubricating groove

Temperature range

T _{min}	-30 °C	Operating temperature min.
T _{max}	200 °C	Operating temperature max.

Calculation factors

e	0,35	Limiting value of Fa/Fr for the applicability of diff. Values of factors X and Y
Y ₁	1,91	Dynamic axial load factor
Y ₂	2,85	Dynamic axial load factor
Y ₀	1,87	Static axial load factor