



FAG



X-life

22315-E1-XL-K

Spherical Roller Bearing

Spherical roller bearings 223...-E1-K, main dimensions to DIN 635-2, with tapered bore, taper 1:12

Technical information



Your current product variant

Design	E1	Without central rip
Bore type	K	Tapered, taper 1:12
Cage	JPA	Sheet metal cage
Radial internal clearance	CN (Group N)	Normal internal clearance
Relubrication facility	Standard	

Main Dimensions & Performance Data

d	75 mm	Bore diameter
D	160 mm	Outside diameter
B	55 mm	Width
C _r	445.000 N	Basic dynamic load rating, radial
C _{0r}	450.000 N	Basic static load rating, radial
C _{ur}	42.000 N	Fatigue load limit, radial
n _G	4.500 1/min	Limiting speed
n _{gr}	3.550 1/min	Reference speed
≈m	5,174 kg	Weight



Mounting dimensions

$d_{a \min}$	87 mm	Minimum diameter shaft shoulder
$d_{a \max}$	92 mm	Maximum diameter of shaft shoulder
$D_{a \max}$	148 mm	Maximum diameter of housing shoulder
$r_{a \max}$	2,1 mm	Maximum recess radius
$d_{b \min}$	82 mm	Minimum cavity diameter of the sleeve
$B_{a \min}$	5 mm	Minimum cavity width of the sleeve

Dimensions

$r_{\min}$	2,1 mm	Minimum chamfer dimension
D_1	136,3 mm	Bore diameter outer ring
d_2	92,4 mm	Raceway diameter of the inner ring
d_s	4,8 mm	Diameter lubrication hole
n_s	9,5 mm	Width of lubricating groove

Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	200 °C	Operating temperature max.

Calculation factors

e	0,34	Limiting value of F_a/F_r for the applicability of diff. Values of factors X and Y
Y_1	1,99	Dynamic axial load factor
Y_2	2,96	Dynamic axial load factor
Y_0	1,94	Static axial load factor

Additional information

H2315	Adapter sleeve
AHX2315G	Withdrawal sleeve



Characteristics



Radial load



Axial load in one direction



Axial load in two directions



Grease Lubrication



Oil Lubrication



Not sealed



Static angular error and misalignment



Dynamic angular error and misalignment