
**FAG****22232-E1A-XL-M-C3**

Spherical Roller Bearing

Spherical roller bearing 222...-E1A-XL-M,
symmetric 2 outer ribs

X-life

Technical information



Your current product variant

Design	E1A	Without central rip
Bore type	Z	Cylindrical
Cage	M	Brass Cage
Radial internal clearance	C3 (Group 3)	Internal clearance larger than CN
Relubrication facility	Standard	

Main Dimensions & Performance Data

d	160 mm	Bore diameter
D	290 mm	Outside diameter
B	80 mm	Width
C _r	1.150.000 N	Basic dynamic load rating, radial
C _{0r}	1.400.000 N	Basic static load rating, radial
C _{ur}	129.000 N	Fatigue load limit, radial
n _G	2.650 1/min	Limiting speed
n _{gr}	1.900 1/min	Reference speed
≈m	22,981 kg	Weight

Mounting dimensions

d _{a min}	174 mm	Minimum diameter shaft shoulder
D _{a max}	276 mm	Maximum diameter of housing shoulder
r _{a max}	2,5 mm	Maximum recess radius



Dimensions

r_{min}	3 mm	Minimum chamfer dimension
D_1	258,2 mm	Bore diameter outer ring
d_2	190,9 mm	Raceway diameter of the inner ring
d_s	8 mm	Diameter lubrication hole
n_s	15 mm	Width of lubricating groove

Temperature range

T_{min}	-30 °C	Operating temperature min.
T_{max}	200 °C	Operating temperature max.

Calculation factors

e	0,26	Limiting value of F_a/F_r for the applicability of diff. Values of factors X and Y
Y_1	2,64	Dynamic axial load factor
Y_2	3,93	Dynamic axial load factor
Y_0	2,58	Static axial load factor

Characteristics

-  Radial load
-  Axial load in one direction
-  Axial load in two directions
-  Grease Lubrication
-  Oil Lubrication
-  Static angular error and misalignment