



**FAG****22316-E1A-XL-K-M-C3**

Spherical Roller Bearing

Spherical roller bearing 223...-E1A-XL-K-M,
symmetric 2 outer ribs**X-life**

Technical information



Your current product variant

Design	E1A	Without central rip
Bore type	K	Tapered, taper 1:12
Cage	M	Brass Cage
Radial internal clearance	C3 (Group 3)	Internal clearance larger than CN
Relubrication	Standard	

Main Dimensions & Performance Data

d	80 mm	Bore diameter
D	170 mm	Outside diameter
B	58 mm	Width
C _r	495.000 N	Basic dynamic load rating, radial
C _{0r}	510.000 N	Basic static load rating, radial
C _{ur}	46.500 N	Fatigue load limit, radial
n _G	4.250 1/min	Limiting speed
n _{gr}	3.400 1/min	Reference speed
≈m	6,098 kg	Weight



Mounting dimensions

$d_{a \min}$	92 mm	Minimum diameter shaft shoulder
$D_{a \max}$	158 mm	Maximum diameter of housing shoulder
$r_{a \max}$	2,1 mm	Maximum recess radius
$d_{a \max}$	98 mm	Maximum diameter of shaft shoulder
$d_{b \min}$	88 mm	Minimum cavity diameter of the sleeve
$B_{a \min}$	5 mm	Minimum cavity width of the sleeve

Dimensions

$r_{\min}$	2,1 mm	Minimum chamfer dimension
D_1	145,1 mm	Bore diameter outer ring
d_2	98,3 mm	Raceway diameter of the inner ring
d_s	4,8 mm	Diameter lubrication hole
n_s	9,5 mm	Width of lubricating groove

Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	200 °C	Operating temperature max.

Calculation factors

e	0,34	Limiting value of F_a/F_r for the applicability of diff. Values of factors X and Y
Y_1	1,99	Dynamic axial load factor
Y_2	2,96	Dynamic axial load factor
Y_0	1,94	Static axial load factor

Additional information

H2316	Adapter sleeve
AHX2316	Withdrawal sleeve