

**FAG****22322-E1A-XL-K-M** **Spherical Roller Bearing**

Spherical roller bearing 223...-E1A-XL-K-M,
symmetric 2 outer ribs

X-life**Technical information****Your current product variant**

Design	E1A	Without central rip
Bore type	K	Tapered, taper 1:12
Cage	M	Brass Cage
Radial internal clearance	CN (Group N)	Normal internal clearance
Relubrication facility	Standard	

Main Dimensions & Performance Data

d	110 mm	Bore diameter
D	240 mm	Outside diameter
B	80 mm	Width
C _r	950.000 N	Basic dynamic load rating, radial
C _{0r}	1.070.000 N	Basic static load rating, radial
C _{ur}	93.000 N	Fatigue load limit, radial
n _G	3.000 1/min	Limiting speed
n _{gr}	2.130 1/min	Reference speed
≈m	17,254 kg	Weight



Mounting dimensions

$d_{a \min}$	124 mm	Minimum diameter shaft shoulder
$D_{a \max}$	226 mm	Maximum diameter of housing shoulder
$r_{a \max}$	2,5 mm	Maximum recess radius
$d_{a \max}$	135 mm	Maximum diameter of shaft shoulder
$d_{b \min}$	121 mm	Minimum cavity diameter of the sleeve
$B_{a \min}$	7 mm	Minimum cavity width of the sleeve

Dimensions

$r_{\min}$	3 mm	Minimum chamfer dimension
D_1	204,9 mm	Bore diameter outer ring
d_2	143,1 mm	Raceway diameter of the inner ring
d_s	8 mm	Diameter lubrication hole
n_s	15 mm	Width of lubricating groove

Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	200 °C	Operating temperature max.

Calculation factors

e	0,33	Limiting value of F_a/F_r for the applicability of diff. Values of factors X and Y
Y_1	2,07	Dynamic axial load factor
Y_2	3,09	Dynamic axial load factor
Y_0	2,03	Static axial load factor

Additional information

H2322	Adapter sleeve
AHX2322G	Withdrawal sleeve