

**FAG****23972-MB**

Spherical Roller Bearing

Spherical roller bearing 239...-MB, symmetric
3 ribs

Technical information



Your current product variant

Bore type	Z	Cylindrical
Cage	MB	Solid brass cage
Radial internal clearance	CN (Group N)	Normal internal clearance
Relubrication facility	Standard	

Main Dimensions & Performance Data

d	360 mm	Bore diameter
D	480 mm	Outside diameter
B	90 mm	Width
C _r	1.440.000 N	Basic dynamic load rating, radial
C _{0r}	3.200.000 N	Basic static load rating, radial
C _{ur}	216.000 N	Fatigue load limit, radial
n _G	1.540 1/min	Limiting speed
n _{gr}	800 1/min	Reference speed
≈m	45,235 kg	Weight

Mounting dimensions

d _{a min}	372,4 mm	Minimum diameter shaft shoulder
D _{a max}	467,6 mm	Maximum diameter of housing shoulder
r _{a max}	2,5 mm	Maximum recess radius



Dimensions

r_{min}	3 mm	Minimum chamfer dimension
D_1	447,1 mm	Bore diameter outer ring
d_s	9,5 mm	Diameter lubrication hole
n_s	17,7 mm	Width of lubricating groove

Temperature range

T_{min}	-30 °C	Operating temperature min.
T_{max}	200 °C	Operating temperature max.

Calculation factors

e	0,17	Limiting value of F_a/F_r for the applicability of diff. Values of factors X and Y
Y_1	4,05	Dynamic axial load factor
Y_2	6,04	Dynamic axial load factor
Y_0	3,96	Static axial load factor

Characteristics

	Radial load
	Axial load in one direction
	Axial load in two directions
	Grease Lubrication
	Oil Lubrication
	Not sealed
	Large bearing
	Static angular error and misalignment
	Dynamic angular error and misalignment