



**FAG****22315-E1A-XL-M-C3**

Spherical Roller Bearing

Spherical roller bearing 223...-E1A-XL-M,
symmetric 2 outer ribs**X-life**

Technical information



Your current product variant

Design	E1A	Without central rip
Bore type	Z	Cylindrical
Cage	M	Brass Cage
Radial internal clearance	C3 (Group 3)	Internal clearance larger than CN
Relubrication	Standard	

Main Dimensions & Performance Data

d	75 mm	Bore diameter
D	160 mm	Outside diameter
B	55 mm	Width
C _r	445.000 N	Basic dynamic load rating, radial
C _{0r}	450.000 N	Basic static load rating, radial
C _{ur}	41.500 N	Fatigue load limit, radial
n _G	4.500 1/min	Limiting speed
n _{gr}	3.550 1/min	Reference speed
≈m	5,12 kg	Weight

Mounting dimensions

d _{a min}	87 mm	Minimum diameter shaft shoulder
D _{a max}	148 mm	Maximum diameter of housing shoulder
r _{a max}	2,1 mm	Maximum recess radius



Dimensions

r _{min}	2,1 mm	Minimum chamfer dimension
D ₁	136,3 mm	Bore diameter outer ring
d ₂	92,4 mm	Raceway diameter of the inner ring
d _s	4,8 mm	Diameter lubrication hole
n _s	9,5 mm	Width of lubricating groove

Temperature range

T _{min}	-30 °C	Operating temperature min.
T _{max}	200 °C	Operating temperature max.

Calculation factors

e	0,34	Limiting value of Fa/Fr for the applicability of diff. Values of factors X and Y
Y ₁	1,99	Dynamic axial load factor
Y ₂	2,96	Dynamic axial load factor
Y ₀	1,94	Static axial load factor