



**FAG****22322-E1A-XL-M**

Spherical Roller Bearing

Spherical roller bearing 223...-E1A-XL-M,
symmetric 2 outer ribs

X-life

Technical information



Your current product variant

Design	E1A	Without central rip
Bore type	Z	Cylindrical
Cage	M	Brass Cage
Radial internal clearance	CN (Group N)	Normal internal clearance
Relubrication	Standard	

Main Dimensions & Performance Data

d	110 mm	Bore diameter
D	240 mm	Outside diameter
B	80 mm	Width
C _r	950.000 N	Basic dynamic load rating, radial
C _{0r}	1.070.000 N	Basic static load rating, radial
C _{ur}	93.000 N	Fatigue load limit, radial
n _G	3.000 1/min	Limiting speed
n _{gr}	2.130 1/min	Reference speed
≈m	17,592 kg	Weight

Mounting dimensions

d _{a min}	124 mm	Minimum diameter shaft shoulder
D _{a max}	226 mm	Maximum diameter of housing shoulder
r _{a max}	2,5 mm	Maximum recess radius



Dimensions

r _{min}	3 mm	Minimum chamfer dimension
D ₁	204,9 mm	Bore diameter outer ring
d ₂	143,1 mm	Raceway diameter of the inner ring
d _s	8 mm	Diameter lubrication hole
n _s	15 mm	Width of lubricating groove

Temperature range

T _{min}	-30 °C	Operating temperature min.
T _{max}	200 °C	Operating temperature max.

Calculation factors

e	0,33	Limiting value of Fa/Fr for the applicability of diff. Values of factors X and Y
Y ₁	2,07	Dynamic axial load factor
Y ₂	3,09	Dynamic axial load factor
Y ₀	2,03	Static axial load factor