

**NA49/22-XL**

Radial roller bearing

Radial roller bearing NA..-XL

X-life

Technical information

**Your current product variant**

Cage	Standard	
Radial internal clearance	CN (Group N)	Normal internal clearance
Lubrication hole	With	With
Coating	Without	
Type of Seal	Without	
Rail connector	Without	
Number of rows	1	Single-row design

Main Dimensions & Performance Data

d	22 mm	Bore diameter
D	39 mm	Outside diameter
B	17 mm	Width
C _r	26.000 N	Basic dynamic load rating, radial
C _{0r}	29.500 N	Basic static load rating, radial
C _{ur}	5.400 N	Fatigue load limit, radial
n _G	15.300 1/min	Limiting speed
n _G Grease	9.200 1/min	Limiting speed for grease lubrication
n _{gr}	8.100 1/min	Reference speed
m	81,71 g	Weight



Dimensions

r _{min}	0,3 mm	Minimum chamfer dimension
F	28 mm	Raceway diameter inner ring
s	0,8 mm	Axial displacement

Temperature range

T _{min}	-30 °C	Operating temperature min.
T _{max}	120 °C	Operating temperature max.

Characteristics

-  Radial load
-  Grease Lubrication
-  Oil Lubrication
-  Not sealed
-  Small design envelope