

**FAG****23138-E1A-XL-K-M-C3** **Spherical Roller Bearing**

Spherical roller bearings 231...-E1A-K, main dimensions to DIN 635-2, with tapered bore, taper 1:12

X-life

Technical information

**Your current product variant**

Design	E1A	Without central rip
Bore type	K	Tapered, taper 1:12
Cage	M	Brass Cage
Radial internal clearance	C3 (Group 3)	Internal clearance larger than CN
Relubrication facility	Standard	
Special material	Standard	

Main Dimensions & Performance Data

d	190 mm	Bore diameter
D	320 mm	Outside diameter
B	104 mm	Width
C _r	1.610.000 N	Basic dynamic load rating, radial
C _{0r}	2.220.000 N	Basic static load rating, radial
C _{ur}	222.000 N	Fatigue load limit, radial
n _G	2.070 1/min	Limiting speed
n _{gr}	1.260 1/min	Reference speed
≈m	32,723 kg	Weight



Mounting dimensions

d _{a min}	204 mm	Minimum diameter shaft shoulder
D _{a max}	306 mm	Maximum diameter of housing shoulder
r _{a max}	2,5 mm	Maximum recess radius
d _{a max}	216 mm	Maximum diameter of shaft shoulder
d _{b min}	202 mm	Minimum cavity diameter of the sleeve
B _{a min}	9 mm	Minimum cavity width of the sleeve

Dimensions

r _{min}	3 mm	Minimum chamfer dimension
D ₁	281,6 mm	Bore diameter outer ring
d _s	8 mm	Diameter lubrication hole
n _s	15 mm	Width of lubricating groove

Temperature range

T _{min}	-30 °C	Operating temperature min.
T _{max}	200 °C	Operating temperature max.

Calculation factors

e	0,3	Limiting value of Fa/Fr for the applicability of diff. Values of factors X and Y
Y ₁	2,28	Dynamic axial load factor
Y ₂	3,39	Dynamic axial load factor
Y ₀	2,23	Static axial load factor

Additional information

H3138	Adapter sleeve
AH3138G	Withdrawal sleeve



Characteristics

-  Radial load
-  Axial load in one direction
-  Axial load in two directions
-  Grease Lubrication
-  Oil Lubrication
-  Not sealed
-  Large bearing
-  Static angular error and misalignment
-  Dynamic angular error and misalignment