



**FAG****23222-E1A-XL-M-C3**

Spherical Roller Bearing

Spherical roller bearings 232...-E1A, main dimensions to DIN 635-2

X-life

Technical information



Your current product variant

Design	E1A	Without central rip
Bore type	Z	Cylindrical
Cage	M	Brass Cage
Radial internal clearance	C3 (Group 3)	Internal clearance larger than CN
Relubrication	Standard	

Main Dimensions & Performance Data

d	110 mm	Bore diameter
D	200 mm	Outside diameter
B	69,8 mm	Width
C _r	710.000 N	Basic dynamic load rating, radial
C _{0r}	870.000 N	Basic static load rating, radial
C _{ur}	73.000 N	Fatigue load limit, radial
n _G	3.250 1/min	Limiting speed
n _{gr}	2.100 1/min	Reference speed
≈m	9,557 kg	Weight

Mounting dimensions

d _{a min}	122 mm	Minimum diameter shaft shoulder
D _{a max}	188 mm	Maximum diameter of housing shoulder
r _{a max}	2,1 mm	Maximum recess radius



Dimensions

$r_{\min}$	2,1 mm	Minimum chamfer dimension
D_1	172,7 mm	Bore diameter outer ring
d_s	4,8 mm	Diameter lubrication hole
n_s	9,5 mm	Width of lubricating groove

Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	200 °C	Operating temperature max.

Calculation factors

e	0,33	Limiting value of F_a/F_r for the applicability of diff. Values of factors X and Y
Y_1	2,06	Dynamic axial load factor
Y_2	3,06	Dynamic axial load factor
Y_0	2,01	Static axial load factor

Characteristics

	Radial load
	Axial load in one direction
	Axial load in two directions
	Grease Lubrication
	Oil Lubrication
	Not sealed
	Static angular error and misalignment
	Dynamic angular error and misalignment