


**FAG****7602040-TVP** [🔗](#)

Axial angular contact ball bearing

Axial angular contact ball bearing 7602...-TVP,
single direction, no screw mounting

Technical information



Your current product variant

Cage	TVP	Plastic cage
Type of Seal	Without	
Arrangement bearing set	Standard	Single bearing
Lubricant	Without	Not greased

Main Dimensions & Performance Data

d	40 mm	Bore diameter
	0 mm	Bore diameter upper tolerance
	-0,006 mm	Bore diameter lower tolerance
D	80 mm	Outside diameter
	0 mm	Outside diameter upper tolerance
	-0,007 mm	Outside diameter lower tolerance
B	18 mm	Width
	0 mm	Width upper tolerance
	-0,12 mm	Width lower tolerance
C _a	39.500 N	Basic dynamic load rating, axial
C _{0a}	106.000 N	Basic static load rating, axial
C _{ua}	4.800 N	Fatigue load limit, axial
n _G Grease	4.900 1/min	Limiting speed for grease lubrication
n _g	2.800 1/min	Thermally safe operating speed
≈m	0,433 kg	Weight



Mounting dimensions

D_a	69,5 mm	Diameter of housing
D_a	H12	Diameter of housing clearance
d_a	53,5 mm	Diameter shaft
d_a	h12	Diameter shaft clearance

Dimensions

r_{min}	1,1 mm	Minimum chamfer dimension
$r_{1 min}$	1,1 mm	Minimum chamfer dimension
a	62,5 mm	Distance between the apexes of the pressure cones
α	60 °	Contact angle

Temperature range

T_{min}	-30 °C	Operating temperature min.
T_{max}	120 °C	Operating temperature max.

Additional information

M_R	0,17 Nm	Bearing frictional torque
c_{aL}	1.190 N/μm	Rigidity axial
	2 μm	Axial runout
	ZM40	Recommended INA precision locknut for radial locking
	AM40	Recommended INA precision locknut for axial locking
M_A	55 Nm	Tightening torque for the recommended INA precision locknut
	13.330 N	Required locknut force axial



Characteristics

-  Radial load
-  Axial load in one direction
-  Grease Lubrication
-  Not sealed