


**FAG****7603025-TVP** [🔗](#)

Axial angular contact ball bearing

Axial angular contact ball bearings 7603,
single direction, with contact angle $\alpha = 60^\circ$,
restricted tolerances

Technical information



Your current product variant

Cage	TVP	Plastic cage
Type of Seal	Without	
Arrangement bearing set	Standard	Single bearing
Lubricant	Without	Not greased

Main Dimensions & Performance Data

d	25 mm	Bore diameter
	0 mm	Bore diameter upper tolerance
	-0,005 mm	Bore diameter lower tolerance
D	62 mm	Outside diameter
	0 mm	Outside diameter upper tolerance
	-0,007 mm	Outside diameter lower tolerance
B	17 mm	Width
	0 mm	Width upper tolerance
	-0,12 mm	Width lower tolerance
C _a	29.500 N	Basic dynamic load rating, axial
C _{0a}	68.000 N	Basic static load rating, axial
C _{ua}	3.100 N	Fatigue load limit, axial
n _G Grease	6.800 1/min	Limiting speed for grease lubrication
n _g	3.800 1/min	Thermally safe operating speed
m	0,266 kg	Weight



Mounting dimensions

D _a	52 mm	Diameter of housing
D _a	H12	Diameter of housing clearance
d _a	38 mm	Diameter shaft
d _a	h12	Diameter shaft clearance

Dimensions

r _{min}	1,1 mm	Minimum chamfer dimension
r _{1 min}	1,1 mm	Minimum chamfer dimension
a	47,5 mm	Distance between the apexes of the pressure cones
α	60 °	Contact angle

Temperature range

T _{min}	-30 °C	Operating temperature min.
T _{max}	120 °C	Operating temperature max.

Additional information

M _R	0,09 Nm	Bearing frictional torque
c _{aL}	917 N/μm	Rigidity axial
	2 μm	Axial runout
	ZM25	Recommended INA precision locknut for radial locking
	AM25	Recommended INA precision locknut for axial locking
M _A	40 Nm	Tightening torque for the recommended INA precision locknut
	14.480 N	Required locknut force axial



Characteristics

-  Radial load
-  Axial load in one direction
-  Grease Lubrication
-  Not sealed