



**FAG****22332-BEA-XL-MA1-T41A**

Spherical Roller Bearing

Spherical roller bearing 223...-BEA-XL-MA1-T41A, symmetric 2 outer ribs with rib washer

X-life

Technical information



Your current product variant

Design	BEA	With lose center lip ring
Bore type	Z	Cylindrical
Cage	MA1	Solid brass cage
Radial internal clearance	C4 (Group 4)	Internal clearance larger than C3
Relubrication	Standard	
Locating feature, bearing outer ring	Without	
Handling thread holes	Without	
Special material	Standard	
Spherical roller bearing for vibrating screens	T41A	For vibrating screens

Main Dimensions & Performance Data

d	160 mm	Bore diameter
D	340 mm	Outside diameter
B	114 mm	Width
C _r	1.680.000 N	Basic dynamic load rating, radial
C _{0r}	1.990.000 N	Basic static load rating, radial
C _{ur}	157.000 N	Fatigue load limit, radial
n _G	2.250 1/min	Limiting speed
n _{gr}	1.420 1/min	Reference speed
≈m	51,33 kg	Weight



Mounting dimensions

$d_{a \min}$	177 mm	Minimum diameter shaft shoulder
$D_{a \max}$	323 mm	Maximum diameter of housing shoulder
$r_{a \max}$	3 mm	Maximum recess radius
$d_{a \max}$	191 mm	Maximum diameter of shaft shoulder
$d_{b \min}$	174 mm	Minimum cavity diameter of the sleeve
$B_{a \min}$	8 mm	Minimum cavity width of the sleeve

Dimensions

$r_{\min}$	4 mm	Minimum chamfer dimension
D_1	286,7 mm	Bore diameter outer ring
d_s	9,5 mm	Diameter lubrication hole
n_s	17,7 mm	Width of lubricating groove

Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	200 °C	Operating temperature max.

Calculation factors

e	0,35	Limiting value of F_a/F_r for the applicability of diff. Values of factors X and Y
Y_1	1,94	Dynamic axial load factor
Y_2	2,88	Dynamic axial load factor
Y_0	1,89	Static axial load factor



Characteristics



Radial load



Axial load in one direction



Axial load in two directions



Grease Lubrication



Oil Lubrication



Not sealed



Static angular error and misalignment



Dynamic angular error and misalignment