



FAG

29413-E1-XL



Axial spherical roller bearing

Axial spherical roller bearing 294..-E1-XL, no flanging ring



X-life

Technical information



Your current product variant

Heat treatment	Standard	Standard
Locating feature, housing washer	Without	
Cage	JP	Sheet metal cage
Handling thread holes	Without	
Constricted width and inclination variation	Standard	
Test certificate	Without	

Main Dimensions & Performance Data

d	65 mm	Bore diameter
D	140 mm	Outside diameter
T	45 mm	Height
C _a	495.000 N	Basic dynamic load rating, axial
C _{0a}	1.160.000 N	Basic static load rating, axial
C _{ua}	139.000 N	Fatigue load limit, axial
n _G	5.500 1/min	Limiting speed
n _{gr}	2.600 1/min	Reference speed
≈m	3,04 kg	Weight



Mounting dimensions

d _{a min}	100 mm	Minimum diameter shaft shoulder
D _{a max}	115 mm	Maximum diameter of housing shoulder
D _{b min}	143 mm	Minimum bore diameter housing
d _{b max}	72 mm	Maximum distance sleeve
r _{a max}	2 mm	Maximum recess radius

Dimensions

D ₁	91,5 mm	Bore diameter housing washer
d ₁	125,2 mm	Rip diameter shaft washer
r _{min}	2 mm	Minimum chamfer dimension
T ₁	22 mm	Height of the housing washer
T ₃	29,5 mm	Height of the shaft washer
T ₅	40,5 mm	Distance shaft washer - cage
A	42 mm	Distance of the center point

Temperature range

T _{min}	-30 °C	Operating temperature min.
T _{max}	200 °C	Operating temperature max.

Characteristics

- 

Radial load
- 

Axial load in one direction
- 

Grease Lubrication
- 

Oil Lubrication
- 

Not sealed
- 

Static angular error and misalignment
- 

Dynamic angular error and misalignment