



**FAG****23134-E1A-XL-K-M**

Spherical Roller Bearing

Spherical roller bearings 231...-E1A-K, main dimensions to DIN 635-2, with tapered bore, taper 1:12

X-life

Technical information



Your current product variant

Design	E1A	Without central rip
Bore type	K	Tapered, taper 1:12
Cage	M	Brass Cage
Radial internal clearance	CN (Group N)	Normal internal clearance
Relubrication	Standard	
Special material	Standard	

Main Dimensions & Performance Data

d	170 mm	Bore diameter
D	280 mm	Outside diameter
B	88 mm	Width
C _r	1.220.000 N	Basic dynamic load rating, radial
C _{0r}	1.690.000 N	Basic static load rating, radial
C _{ur}	177.000 N	Fatigue load limit, radial
n _G	2.380 1/min	Limiting speed
n _{gr}	1.460 1/min	Reference speed
≈m	20,7 kg	Weight



Mounting dimensions

d _{a min}	182 mm	Minimum diameter shaft shoulder
D _{a max}	268 mm	Maximum diameter of housing shoulder
r _{a max}	2,1 mm	Maximum recess radius
d _{a max}	193 mm	Maximum diameter of shaft shoulder
d _{b min}	180 mm	Minimum cavity diameter of the sleeve
B _{a min}	8 mm	Minimum cavity width of the sleeve

Dimensions

r _{min}	2,1 mm	Minimum chamfer dimension
D ₁	248,1 mm	Bore diameter outer ring
d _s	8 mm	Diameter lubrication hole
n _s	15 mm	Width of lubricating groove

Temperature range

T _{min}	-30 °C	Operating temperature min.
T _{max}	200 °C	Operating temperature max.

Calculation factors

e	0,28	Limiting value of Fa/Fr for the applicability of diff. Values of factors X and Y
Y ₁	2,37	Dynamic axial load factor
Y ₂	3,53	Dynamic axial load factor
Y ₀	2,32	Static axial load factor

Additional information

H3134	Adapter sleeve
AH3134A	Withdrawal sleeve



Characteristics

-  Radial load
-  Axial load in one direction
-  Axial load in two directions
-  Grease Lubrication
-  Oil Lubrication
-  Not sealed
-  Static angular error and misalignment
-  Dynamic angular error and misalignment