



**FAG****20217-MB** [↗](#)

Barrel roller bearing

Barrel roller bearing 202...-MB

Technical information



Your current product variant

Bore type	Z	Cylindrical
Cage	MB	Solid brass cage
Radial internal clearance	CN (Group N)	Normal internal clearance

Main Dimensions & Performance Data

d	85 mm	Bore diameter
D	150 mm	Outside diameter
B	28 mm	Width
C _r	155.000 N	Basic dynamic load rating, radial
C _{0r}	201.000 N	Basic static load rating, radial
C _{ur}	20.800 N	Fatigue load limit, radial
n _G	4.750 1/min	Limiting speed
≈m	2,175 kg	Weight

Mounting dimensions

d _{a min}	96 mm	Minimum diameter shaft shoulder
D _{a max}	139 mm	Maximum diameter of housing shoulder
r _{a max}	2 mm	Maximum recess radius

Dimensions

r _{min}	2 mm	Minimum chamfer dimension
D ₁	133,9 mm	Bore diameter outer ring



Temperature range

T_{min}	-30 °C	Operating temperature min.
T_{max}	200 °C	Operating temperature max.

Characteristics

-  Radial load
-  Axial load in one direction
-  Axial load in two directions
-  Grease Lubrication
-  Oil Lubrication
-  Not sealed
-  Static angular error and misalignment
-  Dynamic angular error and misalignment