




KSR16-L0-08-10-16-08

Roller chain idler sprocket unit

Roller chain idler sprocket units KSR...L0,
sprocket made from steel or sintered iron

Technical information



Main Dimensions & Performance Data

d	16,2 mm	Bore diameter
d	0,1 mm	Upper tolerance
d	0 mm	Lower tolerance
C 1	7 mm	Thickness of sprocket
D 0	65,1 mm	Pitch circle diameter (gearing)
D k	70,5 mm	Tip diameter (gearing)
≈m	0,16 kg	Weight

Mounting dimensions

p	12,7 mm	Tooth set
z	16	Number of teeth
x		ISO chain

Dimensions

C 2	1,1 mm	Chamfer width
D	40 mm	Outside diameter
C	12 mm	Width, outer ring
B	18,3 mm	Width inner ring