

**FAG****234409-M-SP** [🔗](#)**Axial angular contact ball bearing**

Axial angular contact ball bearings 2344, double direction, separable, restricted tolerances

Technical information**Your current product variant**

Cage	M	Brass Cage
Tolerance class	SP	Tolerance class SP

Main Dimensions & Performance Data

d	45 mm	Bore diameter
D	75 mm	Outside diameter
B	38 mm	Width
C	19 mm	Width, outer ring
C _a	25.000 N	Basic dynamic load rating, axial
C _{0a}	67.000 N	Basic static load rating, axial
C _{ua}	6.200 N	Fatigue load limit, axial
n _G Grease	7.500 1/min	Limiting speed for grease lubrication
n _G Oil	10.000 1/min	Limiting speed for oil lubrication
≈m	0,584 kg	Weight



Mounting dimensions

d_a	57,5 mm	Diameter shaft shoulder
d_a	h12	Diameter shaft shoulder clearance
D_a	70 mm	Shoulder diameter outer ring
D_a	H12	Shoulder diameter outer ring clearance
$r_{a \max}$	1 mm	Maximum recess radius
$r_{a1 \max}$	0,15 mm	Maximum recess radius
α	60 °	Contact angle
a	125 mm	Distance between the apexes of the pressure cones

Dimensions

d_1	65 mm	Rip diameter shaft washer
B_1	9,5 mm	Height wave disc
$r_{\min}$	1 mm	Minimum chamfer dimension
$r_{1 \min}$	0,15 mm	Minimum chamfer dimension
d_s	3,2 mm	Diameter lubrication hole
n_s	4,8 mm	Width of lubricating groove

Temperature range

$T_{\min}$	-30 °C	Operating temperature min.
$T_{\max}$	150 °C	Operating temperature max.

Additional information

c_a	387 N/μm	Axial rigidity
K_{aE}	514 N	Lift-off force
F_v	180 N	Preload force



Characteristics

-  Radial load
-  Axial load in one direction
-  Axial load in two directions
-  Grease Lubrication
-  Oil Lubrication
-  Not sealed