




06.09.2026, 09:00:00 UTC

FAG29260-E1-MB

Axial spherical roller bearing

Axial spherical roller bearing 292..-E1-MB,
with flanging ring

Technical information



Your current product variant

Heat treatment	Standard	Standard
Cage	MB	Solid brass cage
Locating feature, housing washer	Without	
Handling thread holes	Without	
Constricted width and inclination variation	Standard	
Test certificate	Without	

Main Dimensions & Performance Data

d	300 mm	Bore diameter
D	420 mm	Outside diameter
T	73 mm	Section height
C _a	1.400.000 N	Basic dynamic load rating, axial
C _{0a}	6.200.000 N	Basic static load rating, axial
C _{ua}	660.000 N	Fatigue load limit, axial
n _G	1.500 1/min	Limiting speed
n _{gr}	840 1/min	Reference speed
≈m	30,32 kg	Weight

The data sheet only contains an overview of the technical data of the selected product. Please refer to the additional documentation for this product. For further information, please use the following link on our website: [Contact form](#)



Mounting dimensions

d _{a min}	360 mm	Minimum diameter shaft shoulder
D _{a max}	386 mm	Maximum diameter of housing shoulder
D _{b min}	426 mm	Minimum bore diameter housing
d _{b max}	315 mm	Maximum distance sleeve
r _{a max}	2,5 mm	Maximum recess radius

Dimensions

D ₁	353 mm	Bore diameter housing washer
d ₁	395 mm	Rip diameter shaft washer
r _{min}	3 mm	Minimum chamfer dimension
T ₁	38 mm	Height of the housing washer
T ₂	26 mm	Height of shaft washer
T ₃	44 mm	Height of the shaft washer
T ₄	69 mm	Height of shaft washer, inc. lip ring
A	162 mm	Distance of the center point

Temperature range

T _{min}	-30 °C	Operating temperature min.
T _{max}	200 °C	Operating temperature max.



Characteristics

-  Radial load
-  Axial load in one direction
-  Grease Lubrication
-  Oil Lubrication
-  Not sealed
-  Large bearing
-  Static angular error and misalignment
-  Dynamic angular error and misalignment