


**KSR16-L0-10-10-14-08**

Roller chain idler sprocket unit

Roller chain idler sprocket unit KSR...-
L0-10-10-14-08

Technical information



Main Dimensions & Performance Data

d	16,2 mm	Bore diameter
d	0,1 mm	Upper tolerance
d	0 mm	Lower tolerance
C ₁	8,7 mm	Thickness of sprocket
D ₀	71,3 mm	Pitch circle diameter (gearing)
D _k	78 mm	Tip diameter (gearing)
≈m	0,21 kg	Weight

Mounting dimensions

p	15,875 mm	Tooth set
z	14	Number of teeth
x		ISO chain
x		ANSI chain

Dimensions

C ₂	1,3 mm	Chamfer width
D	40 mm	Outside diameter
C	12 mm	Width, outer ring
B	18,3 mm	Width inner ring

