



LFDL32-SF

Carriage

bogie carriage; clearance-free

Technical information



Your current product variant

Size code	32
Setting	SF

Main Dimensions & Performance Data


H ₁	37 mm	
B	80 mm	
L	100 mm	
≈m	0,85 kg	Weight



View product details on medias

06.09.2026, 05:12:38 UTC

SCHAEFFLER



Mounting dimensions

G 4	M8	
G 6	M8	
H	44,2 mm	Total height of carriage and rail at LFS, -C, -CE, -CEE, -E, -EE, -N, -NZZ
H 2	29,2 mm	
H 2 Tol	0,3	
H 2 Tol	0	
H 3	9 mm	
J B	60 mm	
J B1	54 mm	
J L1	60 mm	
J L2	70 mm	
N 5	21 mm	
T 5	7 mm	

Main dimensions

M A	15 Nm	Tightening torque (standard version)
C y	4.100 N	Basic dynamic load rating in y-direction
C 0y	2.400 N	Basic static load rating in y-direction
C z	6.600 N	Basic dynamic load rating in z-direction
C 0z	4.200 N	Basic static load rating in z-direction
M 0x	30 Nm	Static moment about X-axis
M 0y	130 Nm	Static moment about Y-axis
M 0z	70 Nm	Static moment about Z-axis

Related products

LFR	LFR50/8-6-2Z	Used track roller
LFS	LFS32	Guide rail

The data sheet only contains an overview of the technical data of the selected product. Please refer to the additional documentation for this product. For further information, please use the following link on our website: [Contact form](#)